


# MCS Total Solutions for all your **HVAC/R Control Needs**

# MCS-Nitromag Upgrade Brochure Smardt Water Cooled



#### Click for Brochure Upgrades

This brochure describes a standard upgrade package for the Turbocor series chillers. Each control upgrade installation is unique. It may be necessary to add additional options to the standard upgrade as described in this brochure.

Fill out the brief questionnaire in the back of this brochure and forward to your sales representative for an estimate.



# Example MCS-NitroMag Upgrade Photos

#### **Package with Industrial Control Panel**

#### Concerns:

- Old controls failed
- Wanted controls that were easier to understand and greater reliability, plus better and clear information

#### Equipment:

- Smardt and other brands Water Cooled Chillers
- One to Four Turbocor Compressors
- · One to Four Staging Valves
- Load balancing EXV control
- Modulating condenser water valve

#### Steps Taken:

- · Remove existing controls
- · Install MCS controls
- Reprogram boards for communication
- Provide on-site training and support for contractor to better understand MCS controls.

#### Results:

One Smardt Chiller upgraded with MCS controls and one satisfied customer who is very happy with all the information and data available compared to the competitor's controls.












## MCS-NitroMag-15.4 **Description & Specifications**



Part # MCS-NitroMag-15.4

### **Description**

The MCS-NitroMag-15.4 is a control system containing a Capacitive Touchscreen, and a MCS-NitroMag-N controller. It includes a processor, memory, eMMC Flash, and supporting power circuitry. The Broadcom quad-core processor on the MCS-NitroMag-N delivers a blazing speed of 1.5GHz.

The MCS-NitroMag-N controller connects with MCS Expansion boards and Extension boards, allowing for a maximum of 144 SI inputs, 90 RO outputs, and 36 AO outputs.

The Capacitive touchscreen interface designed to simplify user access with the MCS Expansion Boards and utilizing MCS-Connect to provide both graphics and service mode access to technicians. Highly accurate and does not require calibration - easy to clean glass surface. Works outdoors, bright screen, water resistant, Exceptional Optics - 1280x800 resolution, sharp and vibrant images.

MCS-NitroMag-15.4 comes pre loaded with the MCS-CONNECT program that allows you to view the 'unit's status', 'extended history', 'alerts', 'alarms', setpoints, and more, all in a userfriendly graphic format.

The MCS-NitroMag-15.4 comes with a built-in WiFi interface for Ethernet connectivity, and an onboard WiFi antenna connection mounted on the front of the touchscreen.

It features various connections ports for:

- 2 HDMI ports (1 Standard and 1 Micro port)
- · WiFi antenna connection
- · 12vdc power input connection
- Ethernet port (10 Mbps/100 Mbps/1 GHz)
- · MCS-IO port for communicating with expansion boards.

Includes a MODBUS interface which enables it to act as a Modbus Master using the Modbus RTU protocol, allowing communication with Modbus slave devices for parameter access.

#### **Specifications**

432mm L x 308mm W x 82mm H

Mounting

Door Mount. .....Template included

10 mount studs thru customers enclosure.

MS4745 silicone gasket

NEMA 4 IP66 rated

Indoor or outdoor (Mounted in Nema4 Enclosure)

16.2 Million Colors

1280x800 Resolution

View Angle 70°U, 70°D, 70°L, 70°R

Capacitive Stylus pen

White LED Backlight (Min Life 50,000 Hrs)

Luminance Min. 350 Min. 450 Typical

Touchscreen Surface......UV Degradation Protection

Operating Temperature...... -22°F to 176°F (-30°C to +80°C)

Operating Humidity......90 %RH (Non Condensing) Storage Temperature.....-22°F to 176°F (-30°C to +80°C)

#### Controller

Microprocessor...... Broadcom BCM2711 Quad core Cortex (ARMv8) 64-bit SoC @ 1.5Ghz

INPUT	MINIMUM	NOMINAL	MAXIMUM
VOLTAGE	10	12	12.5
AMPS			2

Flash Memory ...... 16 GB EMMC RAM ......2 GB DDR3 MCS-I/O Comm Port. .......... 1 @ 38,400 baud

RS-485 Ports. ..... 2 @ go up to 115200 baud rate 

HDMI ......2 HDMI 2.0 ports-Standard and Micro WiFi......2.4GHz, 5.0GHz 8.02 b/g/n/ac wireless

USB ......2 USB type B 2.0 ports 480Mbps signalling

Protocols.....BACnet IP, BACnet MSTP, Modbus IP,

Modbus RTU Slave, Modbus RTU Master

(BTL certification pending)

Real Time Clock ......Battery backup(Type BR2032)

Power Detection ......Automatic power fail reset

#### POWER SUPPLY NOT INCLUDED

#### **Packaging**

Ship Weight.....2.00 lb (approx)

5580 Enterprise Pkwy., Fort Myers, FL 33905 Office: 239-694-0089 • Fax: 239-694-0031 www.mcscontrols.com

# MCS-NitroMag-MLB-15.4 INDUSTRIAL CONTROL PANEL **YSTEMS** RoHS Compliant MCS-NITROMAG CONTROLLER

Part # MCS-NITROMAG-MLB-15.4\*

#### **Description**

The MCS-NitroMag-MLB-15.4 Industrial Control Panel is made of powder coated aluminum for durability and longevity. A left hand swing door is mounted with three eight-inch hinges for strength. A key lock is provided for security on the door while still giving easy access of the display. This panel is intended for use in an environment protected from the weather.

The MCS-NitroMag-MLB-15.4 is a control system containing a Capacitive Touchscreen, MCS-NITROMAG Controller, MCS-IO-BASE, MCS-IO-EXT. It includes a processor, memory, eMMC Flash, and supporting power circuitry.

Panel includes the following; 20A, and a 5A Single-Pole Circuit Breaker, a 5 port 10/100/1000 Ethernet Workgroup Switch Industrial rated, Red Alarm Indicator, Yellow Warning Indicator, Emergency Stop Switch and HAND/OFF/AUTO selector Switch.

The MCS-NITROMAG controller comes with a built-in WiFi interface for Ethernet connectivity, and an onboard WiFi antenna connection mounted on the front of the touchscreen.

It features various connections ports for:

- 2 HDMI ports (1 Standard and 1 Micro port)
- 12vdc & 24vdc power input connections
- Ethernet port (10 Mbps/100 Mbps/1 GHz)
- MCS-IO port for communicating with expansion boards

Includes a MODBUS interface which enables it to act as a Modbus Master using the Modbus RTU protocol, allowing communication with Modbus slave devices for parameter access. Power is supplied using a MCS-12V-90W power supply.

There is also an electrical outlet for laptop plug-in power at the panel.

#### **Packaging**

Weight	60 lbs(approx)
Box	24" x 10" x 30"

#### **Specifications**

#### NEMA Rating - Type 2 Control Panel

Enclosure is intended for indoor use primarily to provide a degree of protection against contact with the enclosed equipment and is not protected from liquids.

#### **Industrial Control Panel**

Mounting Holes..... Mounts with four pre drilled 15/32" holes

Rated Voltage (Standard)..... 120VAC or 230VAC 'Phase / Frequency...... 1 Phase / 60Hz

Full Load Current(approx) .... 40A at 120VAC or 20A at 240VAC

Short Circuit Current Rating . 10kA

#### Temp. Range for Control Panel & Touch Screen

16.2 Million Colors

1280x800 Resolution

View Angle 70°U, 70°D, 70°L, 70°R

Capacitive Stylus pen

White LED Backlight (Min Life 50,000 Hrs)

Luminance Min. 350 Min. 450 Typical

Touchscreen Surface....... UV Degradation Protection Operating Temperature..... -22°F to 176°F (-30°C to +80°C) Operating Humidity............ 90 %RH (Non Condensing) Storage Temperature....... -22°F to 176°F (-30°C to +80°C)

#### Controller

Microprocessor..... Broadcom BCM2711 Quad core Cortex (ARMv8) 64-bit SoC @ 1.5Ghz

INPUT	MINIMUM	NOMINAL	MAXIMUM
VOLTAGE	10	12	12.5
AMPS			2

Flash Memory ...... 16 GB EMMC RAM ...... 2 GB DDR3 MCS-I/O Comm Port. ....... 1 @ 38,400 baud RS-485 Ports...... 2 @ go up to 115200 baud rate Ethernet ...... 10 Mbps/100Mbps/1Gbps HDMI .....2 HDMI 2.0 ports-Standard and Micro WiFi ......2.4 GHz, 5.0 GHz 8.02 b/g/n/ac wireless

USB ......2 USB type B 2.0 ports 480Mbps signalling Protocols.....BACnet IP, BACnet MSTP, Modbus IP,

Modbus RTU Slave, Modbus RTU Master (BTL certification cpending)

Real Time Clock ......Battery backup(Type BR2032) Power Detection ...... Automatic power fail reset

#### **Power Supply - Specification**

12vdc power supply.....85vac ~ 264vac AC frequency range......47 ~ 63Hz / 7.5A / 90W

24vdc power supply......85vac ~ 264vac AC frequency range.......47 ~ 63Hz / 4A / 96W

5580 Enterprise Pkwy., Fort Myers, FL 33905 Office: 239-694-0089 • Fax: 239-694-0031 www.mcscontrols.com

<sup>\*</sup> Photo shown is an example of an Industrial Control Panel; some optional equipment may be shown.

<sup>\*\*</sup>The glove needs to have a conductive fabric or material to work with cap touchscreens.

# Example Graphics MCS-Nitromag-15.4

## Touchscreen


The MCS-NitroMag-15.4 capacitive touchscreen interface designed to simplify user access with MCS Expansion boards utilizing MCS-Connect to provide both graphics and service mode access to technicians. Input method: Finger, glove, stylus.


Highly accurate and does not require calibration - easy to clean glass surface. Works outdoors, bright screen, water resistant, Exceptional Optics - 1280x800 resolution, sharp and vibrant images.


MCS-MCS-NitroMag-15.4 comes preloaded with the MCS-CONNECT program that allows you to view the 'unit's status', 'extended history', 'alerts', 'alarms', setpoints, and more, all in a user-friendly graphic format.


#### Standard screens include:

• SYSTEM OVERVIEW, COMPRESSOR OVERVIEW and EVAPORATOR/CONDENSER OVERVIEW









# Example Typical Upgrade with Optional Boards



## MCS-NitroMag-N

The **MCS-NitroMag-N** is a control system containing a processor, memory, eMMC Flash, and supporting power circuitry. The Broadcom quadcore processor delivers a blazing speed of 1.5GHz.

The MCS-NitroMag-N controller connects with MCS Expansion boards and Extension boards, allowing for a maximum of 144 SI inputs, 90 RO outputs, and 36 AO outputs.


The MCS-NitroMag-N comes with a built-in WiFi interface for Ethernet connectivity, and an onboard WiFi antenna connection.

### MCS-IO-Base & MCS-IO-EXT

MCS-IO-BASE has a stand-alone microprocessor which communicates with a MCS-NitroMag over the MCS-I/O port at 38,400 baud. The MCS-IO-BASE has 16 SI inputs, 10 RO outputs, and 4 AO outputs. All data is check summed with auto error correction. Each MCS-IO-BASE board can be powered by a 12VDC regulated power supply and has a automatic power fail reset system.



The MCS-IO-EXT provides a flexible and cost effective way to allow relay output, sensor input and analog output expansion for MCS-NitroMag. Each MCS-IO-EXT can be paired with a MCS-IO-BASE to double the number of inputs and outputs.



## MCS-SI-Base & MCS-SI-EXT


The MCS-SI-BASE provides a flexible and cost effective way to allow sensor input and analog output expansion for the MCS-NitroMag. Each MCS-SI-BASE has a stand-alone microprocessor which communicates with the MCS-Nitromag over the MCS-I/O port at 38,400 baud. The MCS-SI-BASE has 16 SI inputs and 4 AO ouputs. All data is check summed with auto error correction. MCS-SI-BASE

board can be powered by a 12VDC regulated power supply and has a automatic power fail reset system.

The MCS-SI-EXT provides a flexible and cost effective way to allow sensor input and analog output expansion for the MCS MAGNUM. Each MCS-SI-EXT can be paired with a MCS-SI-BASE to double the number of inputs and outputs.

## MCS-RO-Base & MCS-RO-EXT

The MCS-RO-BASE provides a flexible and cost effective way to allow relay output expansion for the MCS-Nitromag. Each MCS-RO-BASE has a stand-alone microprocessor which communicates over the MCS-I/O port at 38,400 baud. All data is check summed with auto error correction. Because



the communication is over a RS-485 long distance two-wire differential network transmission system, the MCS-RO-BASE may be located up to 5,000 feet away.

The MCS-RO-BASE board is powered by a 12VDC regulated power supply.

The MCS-RO-EXT provides a flexible and cost effective way to allow relay output expansion for the MCS NitroMag. Each MCS-RO-EXT can be paired with a MCS-RO-BASE to double the number of outputs.

# Example Typical Control Upgrade

# MCS-PRESSURE TRANSDUCERS



The MCS Pressure Transducers are one of the most economical and durable options on the market for dealing with high-pressure industrial applications.

In addition to being CE and UL approved, MCS transducers are capable of surviving high vibration. They include a cavity built out of solid 17-4 PH stainless steel ¼" SAE Female Flare fitting & Schrader valve; 7/16-20 UNF pipe thread which creates a leak-proof, all metal sealed system that makes the transducers ideal for use with rugged HVAC environments.



## MCS-T100

An extremely fast acting temperature sensor built for demanding environments. It is ideal for high moisture locations with continuous freeze and thaw cycles. The sensor is potted with a thermally conductive RTV Cure Silicon Adhesive to guarantee durability and response. Its high accuracy allows for interchangeability in the field. The large resistance range allows the use of over 1000' of cable with no noticeable effect. The MCS-T100 sensor has the ability to move from 32°F to 212°F in approximately 10 to 15 seconds.

## MCS-Wells/Tubes

The MCS-WELL was designed to be used with the MCS-T100 temperature sensor, although it has other applications. It is used in the 23XL series chillers in the chilled water and condenser water lines. It comes pre-filled with heat conductive compound to aid in temperature to the sensor.





The **MCS-TUBE** can be epoxied to a discharge or suction line on the 23XL series chillers in order to obtain temperature readings without the use of a well. It was designed to be used with the MCS-T100 temperature sensor and comes pre-filled with heat conductive compound to aid in transferring temperature to the sensor.



### MCS-USB-RS485

The MCS-USB-RS485 is a USB to RS485 cable that provides a fast simple way to connect a MCS-MAGNUM to a Laptop or PC.

The MCS-USB-RS485 cable contains a small internal electronic circuit board, which converts USB to RS485 with LED indicators for transmit (TX=Red) and receive (RX=Green).

# Example Typical Control Upgrade

## MCS-EPOXY

- Pre-measured resins and hardeners in one tube
- Easy to use bonds, seals, plugs, molds and rebuilds
- No special tools needed
- Can even harden under water



•	Pressure tested to	. 1300 psi
•	Temperatures up to	.500 degree F
•	Color	. Gray
•	Density	. 15.9 lb/gal (1.9 g/cc)
•	Hardness (Shore D)	. 85
•	Tensile Strength	. 6000 psi
•	Compressive Strength	. 18.000 psi
•	Modulus of Elasticity	.6 x 105 psi
•	Shear Strength	. 700 psi



## MCS-CT500

MCS-CT500 current sensor monitors current flowing to electrical equipment. The magnitude of the current is converted to a linear output voltage between 0.06 to 4.52vdc which can be read as a standard analog input signal. The signal is used by MCS micro controllers for the following:


- 1. For slide valve control on screw machines
- 2. For high amp motor overload protection
- 3. For verification of device on / off

# MCS-VOLTAGE-3PH

The **MCS-VOLTAGE-3PH** measures AC voltage between 200-600 AC. It is designed to monitor the voltage of each phase of the main input power to the unit.

The MCS-VOLTAGE-3PH sensor provides three separate DC voltage outputs that correspond to the AC voltage it is measuring.







## MCS-PHASE-B

The MCS-PHASE-B is a programmable 3-phase line voltage monitor, high temperature LCD display, easy setup and clear diagnostic readout of system faults. The MCS-PHASE-B was specifically designed to protect motors and other 3-phase loads from premature failure and damage due to common voltage faults such as unbalance, over/under voltage, phase loss, reversal, incorrect sequencing and rapid short cycling.

### **Relay Outputs (MCS-IO-BASE)**

#	Output Name	Туре	Description
1-1	SPARE 1-1	Standard	Relay output not used
1-2	SPARE 1-2	Standard	Relay output not used
13	SPARE 1-3	Standard	Relay output not used
1-4	SPARE 1-4	Standard	Relay output not used
1-5	SPARE 1-5	Standard	Relay output not used
1-6	Cmp1I-Lock	Standard	Comp 1 J2 TurboCor Interlock
1-7	Cmp2I-Lock	User Logic	Comp 2 J2 TurboCor Interlock
1-8	Cmp3I-Lock	User Logic	Comp 3 J2 TurboCor Interlock
1-9	Warning	Standard	Warning Light: unit is in a safety condition prior to a safety shutdown
1-10	Alarm	Standard	Alarm Light: unit is in a safety shutdown

### **Relay Outputs (MCS-IO-EXT)**

2-1	Comp 1	Step w∖ EXV	Compressor 1 Run Enable
2-2	SPARE 2-2	Standard	Relay output not used
2-3	SPARE 2-3	Standard	Relay output not used
2-4	SPARE 2-4	Standard	Relay output not used
2-5	SPARE 2-5	Standard	Relay output not used
2-6	SPARE 2-6	Standard	Relay output not used
2-7	SPARE 2-7	Standard	Relay output not used
2-8	SPARE 2-8	Standard	Relay output not used
2-9	SPARE 2-9	Standard	Relay output not used
2-10	SPARE 2-10	Standard	Relay output not used

### **Relay Outputs (MCS-RO-BASE)**

3-1	Comp 2	Step w∖ EXV	Compressor 2 Run Enable
3-2	SPARE 3-2	Standard	Relay output not used
3-3	SPARE 3-3	Standard	Relay output not used
3-4	SPARE 3-4	Standard	Relay output not used
3-5	SPARE 3-5	Standard	Relay output not used
3-6	SPARE 3-6	Standard	Relay output not used
3-7	SPARE 3-7	Standard	Relay output not used
3-8	SPARE 3-8	Standard	Relay output not used
3-9	SPARE 3-9	Standard	Relay output not used
3-10	SPARE 3-10	Standard	Relay output not used

### **Relay Outputs (MCS-RO-EXT)**

#	Output Name	Туре	Description
4-1	Comp 3	Step w∖ EXV	Compressor 3 Run Enable
4-2	SPARE2-2	Standard	Relay output not used
4-3	Cmp1Alarm	Standard	Comp 1 In Alarm Output
4-4	Cmp2Alarm	Standard	Comp 2 In Alarm Output
4-5	Cmp3Alarm	Standard	Comp 3 In Alarm Output
4-6	SPARE4-6	Standard	Relay output not used
4-7	SPARE4-7	Standard	Relay output not used
4-8	SPARE4-8	Standard	Relay output not used
4-9	SPARE4-9	Standard	Relay output not used
4-10	SPARE4-10	Standard	Relay output not used

### Sensor Inputs(MCS-IO-BASE)

#	Output Name	Туре	Description
1-1	ChilWtrIn	MCST100	Chilled Water In Temperature
1-2	ChilWtrOut	MCST100	Chilled Water Leaving Temperature
1-3	CndWtrIn	MCST100	Condenser water incoming temperature
1-4	CndWtrOut	MCST100	Condenser water leaving temperature
1-5	CndLevel	User Defined	Condenser Level Sensor
1-6	LoPsi SW 1	DIGITAL	Mechanical Low Psi Switch Comp 1
1-7	HiPsi SW 1	DIGITAL	Mechanical High Psi Switch Comp 1
1-8	LoPsi SW 2	DIGITAL	Mechanical Low Psi Switch Comp 2
1-9	HiPsi SW 2	DIGITAL	Mechanical High Psi Switch Comp 2
1-10	LoPsi SW 3	DIGITAL	Mechanical Low Psi Switch Comp 3
1-11	HiPsi SW 3	DIGITAL	Mechanical High Psi Switch Comp 3
1-12	CndFlow	DIGITAL	Monitors the condenser flow
1-13	ChwFlow	DIGITAL	Monitors the chilled water flow
1-14	Phaseloss	DIGITAL	Phase loss: phase imbalance
1-15	Run/Stop	DIGITAL	Run/Stop/Hand Switch
1-16	Emg/Stop	DIGITAL	Emergency Stop Switch

### **Sensor Inputs (MCS-IO-EXT)**

#	Output Name	Туре	Description
2-1	Cmp1 Fault	TurboCorFault	Compressor 1 Fault Message
2-2	Ctrl Mode1	ModbusHex	Compressor 1 Control Mode
2-3	IGV Open%	MODBUS	Inlet Guide Vane%-Compressor 1
2-4	SuctPsi 1	MODBUS	Suction Pressure - Compressor 1
2-5	DiscPsi 1	MODBUS	Discharge Pressure - Compressor 1
2-6	CavityTmp1	MODBUS	Cavity Temperature-Compressor 1
2-7	InvertTmp1	MODBUS	Inverter Temperature-Compressor 1
2-8	ChokSpeed1	MODBUS	Choke Speed-Compressor 1
2-9	SurgSpeed1	MODBUS	Surge Speed-Compressor 1
2-10	ActSpeed1	MODBUS	Actual Speed-Compressor 1
2-11	ComPSIRat1	MODBUS	Compressor 1 Pressure Ratio
2-12	Cmp1Amps	MODBUS	Compressor 1 Amperage
2-13	M IGV1STPS	MODBUS	Inlet Guide Vane Steps-Compressor 1
2-14	SPARE 2-14	SPARE	Sensor input not used
2-15	SPARE 2-15	SPARE	Sensor input not used
2-16	SPARE 2-16	SPARE	Sensor input not used

### **Sensor Inputs (MCS-SI-BASE)**

3-1	Cmp2 Fault	TurboCorFault	Compressor 2 Fault Message
3-2	Ctrl Mode2	ModbusHex	Compressor 2 Control Mode
3-3	IGV Open%	MODBUS	Inlet Guide Vane%-Compressor 2
3-4	SuctPsi 2	MODBUS	Suction Pressure - Compressor 2
3-5	DiscPsi 2	MODBUS	Discharge Pressure - Compressor 2
3-6	CavityTmp2	MODBUS	Cavity Temperature-Compressor 2
3-7	InvertTmp2	MODBUS	Inverter Temperature-Compressor 2
3-8	ChokSpeed2	MODBUS	Choke Speed-Compressor 2
3-9	SurgSpeed2	MODBUS	Surge Speed-Compressor 2
3-10	ActSpeed2	MODBUS	Actual Speed-Compressor 2
3-11	ComPSIRat2	MODBUS	Compressor 2 Pressure Ratio
3-12	Cmp2Amps	MODBUS	Compressor 2 Amperage
3-13	M IGV2STPS	MODBUS	Inlet Guide Vane Steps-Compressor 2
3-14	SPARE3 -14	SPARE	Sensor input not used
3-15	SPARE 3-15	SPARE	Sensor input not used
3-16	SPARE 3-16	SPARE	Sensor input not used

### **Sensor Inputs (MCS-SI-EXT)**

#	Output Name	Туре	Description
4-1	Cmp3 Fault	TurboCorFault	Compressor 3 Fault Message
4-2	Ctrl Mode2	ModbusHex	Compressor 3 Control Mode
4-3	IGV Open%	MODBUS	Inlet Guide Vane%-Compressor 3
4-4	SuctPsi 2	MODBUS	Suction Pressure - Compressor 3
4-5	DiscPsi 2	MODBUS	Discharge Pressure - Compressor 3
4-6	CavityTmp2	MODBUS	Cavity Temperature-Compressor 3
4-7	InvertTmp2	MODBUS	Inverter Temperature-Compressor 3
4-8	ChokSpeed2	MODBUS	Choke Speed-Compressor 3
4-9	SurgSpeed2	MODBUS	Surge Speed-Compressor 3
4-10	ActSpeed2	MODBUS	Actual Speed-Compressor 3
4-11	ComPSIRat2	MODBUS	Compressor 3 Pressure Ratio
4-12	Cmp2Amps	MODBUS	Compressor 3 Amperage
4-13	M IGV2STPS	MODBUS	Inlet Guide Vane Steps-Compressor 3
4-14	SPARE 4-14	SPARE	Sensor input not used
4-15	SPARE 4-15	SPARE	Sensor input not used
4-16	SPARE 4-16	SPARE	Sensor input not used

### Sensor Inputs (MCS-SI-BASE#2)

5-1EvapPsiMCS-200Evaporator Pressure5-2DiscPsi 1MCS-500Discharge Pressure 14-3DiscPsi 2MCS-500Discharge Pressure 25-4DiscPsi 3MCS-500Discharge Pressure 35-5LiqPsiMCS-500Liquid Pressure5-6SuctTmp 1MCST100Suction Temperature - Compressor 15-7SuctTmp 2MCST100Suction Temperature - Compressor 25-8SuctTmp 3MCST100Suction Temperature - Compressor 35-9DiscTmp 1MCST100Discharge Temperature - Compressor 15-10DiscTmp 2MCST100Discharge Temperature - Compressor 25-11DiscTmp 3MCST100Discharge Temperature - Compressor 35-12LiqTmpMCST100Discharge Temperature - Compressor 35-12LiqTmpMCST100Liquid Temperature5-13Disable 1DIGITALTurns Off Compressor 15-14Disable 2DIGITALTurns Off Compressor 25-15Disable 3DIGITALTurns Off Compressor 35-16AmbientMCST100Outdoor Air Temperature				
4-3 DiscPsi 2 MCS-500 Discharge Pressure 2  5-4 DiscPsi 3 MCS-500 Discharge Pressure 3  5-5 LiqPsi MCS-500 Liquid Pressure  5-6 SuctTmp 1 MCST100 Suction Temperature - Compressor 1  5-7 SuctTmp 2 MCST100 Suction Temperature - Compressor 2  5-8 SuctTmp 3 MCST100 Suction Temperature - Compressor 3  5-9 DiscTmp 1 MCST100 Discharge Temperature - Compressor 1  5-10 DiscTmp 2 MCST100 Discharge Temperature - Compressor 2  5-11 DiscTmp 3 MCST100 Discharge Temperature - Compressor 3  5-12 LiqTmp MCST100 Liquid Temperature  5-13 Disable 1 DIGITAL Turns Off Compressor 1  5-14 Disable 2 DIGITAL Turns Off Compressor 3  5-15 Disable 3 DIGITAL Turns Off Compressor 3	5-1	EvapPsi	MCS-200	Evaporator Pressure
5-4 DiscPsi 3 MCS-500 Discharge Pressure 3  5-5 LiqPsi MCS-500 Liquid Pressure  5-6 SuctTmp 1 MCST100 Suction Temperature - Compressor 1  5-7 SuctTmp 2 MCST100 Suction Temperature - Compressor 2  5-8 SuctTmp 3 MCST100 Suction Temperature - Compressor 3  5-9 DiscTmp 1 MCST100 Discharge Temperature - Compressor 1  5-10 DiscTmp 2 MCST100 Discharge Temperature - Compressor 2  5-11 DiscTmp 3 MCST100 Discharge Temperature - Compressor 3  5-12 LiqTmp MCST100 Liquid Temperature  5-13 Disable 1 DIGITAL Turns Off Compressor 1  5-14 Disable 2 DIGITAL Turns Off Compressor 2  5-15 Disable 3 DIGITAL Turns Off Compressor 3	5-2	DiscPsi 1	MCS-500	Discharge Pressure 1
5-5 LiqPsi MCS-500 Liquid Pressure  5-6 SuctTmp 1 MCST100 Suction Temperature - Compressor 1  5-7 SuctTmp 2 MCST100 Suction Temperature - Compressor 2  5-8 SuctTmp 3 MCST100 Suction Temperature - Compressor 3  5-9 DiscTmp 1 MCST100 Discharge Temperature - Compressor 1  5-10 DiscTmp 2 MCST100 Discharge Temperature - Compressor 2  5-11 DiscTmp 3 MCST100 Discharge Temperature - Compressor 3  5-12 LiqTmp MCST100 Liquid Temperature  5-13 Disable 1 DIGITAL Turns Off Compressor 1  5-14 Disable 2 DIGITAL Turns Off Compressor 2  5-15 Disable 3 DIGITAL Turns Off Compressor 3	4-3	DiscPsi 2	MCS-500	Discharge Pressure 2
5-6 SuctTmp 1 MCST100 Suction Temperature - Compressor 1 5-7 SuctTmp 2 MCST100 Suction Temperature - Compressor 2 5-8 SuctTmp 3 MCST100 Suction Temperature - Compressor 3 5-9 DiscTmp 1 MCST100 Discharge Temperature - Compressor 1 5-10 DiscTmp 2 MCST100 Discharge Temperature - Compressor 2 5-11 DiscTmp 3 MCST100 Discharge Temperature - Compressor 3 5-12 LiqTmp MCST100 Liquid Temperature 5-13 Disable 1 DIGITAL Turns Off Compressor 1 5-14 Disable 2 DIGITAL Turns Off Compressor 2 5-15 Disable 3 DIGITAL Turns Off Compressor 3	5-4	DiscPsi 3	MCS-500	Discharge Pressure 3
5-7 SuctTmp 2 MCST100 Suction Temperature - Compressor 2 5-8 SuctTmp 3 MCST100 Suction Temperature - Compressor 3 5-9 DiscTmp 1 MCST100 Discharge Temperature - Compressor 1 5-10 DiscTmp 2 MCST100 Discharge Temperature - Compressor 2 5-11 DiscTmp 3 MCST100 Discharge Temperature - Compressor 3 5-12 LiqTmp MCST100 Liquid Temperature 5-13 Disable 1 DIGITAL Turns Off Compressor 1 5-14 Disable 2 DIGITAL Turns Off Compressor 2 5-15 Disable 3 DIGITAL Turns Off Compressor 3	5-5	LiqPsi	MCS-500	Liquid Pressure
5-8 SuctTmp 3 MCST100 Suction Temperature - Compressor 3  5-9 DiscTmp 1 MCST100 Discharge Temperature - Compressor 1  5-10 DiscTmp 2 MCST100 Discharge Temperature - Compressor 2  5-11 DiscTmp 3 MCST100 Discharge Temperature - Compressor 3  5-12 LiqTmp MCST100 Liquid Temperature  5-13 Disable 1 DIGITAL Turns Off Compressor 1  5-14 Disable 2 DIGITAL Turns Off Compressor 2  5-15 Disable 3 DIGITAL Turns Off Compressor 3	5-6	SuctTmp 1	MCST100	Suction Temperature - Compressor 1
5-9 DiscTmp 1 MCST100 Discharge Temperature - Compressor 1  5-10 DiscTmp 2 MCST100 Discharge Temperature - Compressor 2  5-11 DiscTmp 3 MCST100 Discharge Temperature - Compressor 3  5-12 LiqTmp MCST100 Liquid Temperature  5-13 Disable 1 DIGITAL Turns Off Compressor 1  5-14 Disable 2 DIGITAL Turns Off Compressor 2  5-15 Disable 3 DIGITAL Turns Off Compressor 3	5-7	SuctTmp 2	MCST100	Suction Temperature - Compressor 2
5-10 DiscTmp 2 MCST100 Discharge Temperature - Compressor 2  5-11 DiscTmp 3 MCST100 Discharge Temperature - Compressor 3  5-12 LiqTmp MCST100 Liquid Temperature  5-13 Disable 1 DIGITAL Turns Off Compressor 1  5-14 Disable 2 DIGITAL Turns Off Compressor 2  5-15 Disable 3 DIGITAL Turns Off Compressor 3	5-8	SuctTmp 3	MCST100	Suction Temperature - Compressor 3
5-11 DiscTmp 3 MCST100 Discharge Temperature - Compressor 3  5-12 LiqTmp MCST100 Liquid Temperature  5-13 Disable 1 DIGITAL Turns Off Compressor 1  5-14 Disable 2 DIGITAL Turns Off Compressor 2  5-15 Disable 3 DIGITAL Turns Off Compressor 3	5-9	DiscTmp 1	MCST100	Discharge Temperature - Compressor 1
5-12 LiqTmp MCST100 Liquid Temperature  5-13 Disable 1 DIGITAL Turns Off Compressor 1  5-14 Disable 2 DIGITAL Turns Off Compressor 2  5-15 Disable 3 DIGITAL Turns Off Compressor 3	5-10	DiscTmp 2	MCST100	Discharge Temperature - Compressor 2
5-13 Disable 1 DIGITAL Turns Off Compressor 1 5-14 Disable 2 DIGITAL Turns Off Compressor 2 5-15 Disable 3 DIGITAL Turns Off Compressor 3	5-11	DiscTmp 3	MCST100	Discharge Temperature - Compressor 3
5-14 Disable 2 DIGITAL Turns Off Compressor 2 5-15 Disable 3 DIGITAL Turns Off Compressor 3	5-12	LiqTmp	MCST100	Liquid Temperature
5-15 Disable 3 DIGITAL Turns Off Compressor 3	5-13	Disable 1	DIGITAL	Turns Off Compressor 1
·	5-14	Disable 2	DIGITAL	Turns Off Compressor 2
5-16 Ambient MCST100 Outdoor Air Temperature	5-15	Disable 3	DIGITAL	Turns Off Compressor 3
	5-16	Ambient	MCST100	Outdoor Air Temperature

### Sensor Inputs (MCS-SI-EXT#2)

#	Output Name	Туре	Description
6-1	Net R/S	BMS RUN	Building Management interface Run/Stop
6-2	NetReset	BMS CW RSET	Building Management interface target reset
6-3	NetDmdLmt	BMS Dmd FLA%	Building Management interface for Demand %
6-4	SPARE 6-4	SPARE	Sensor input not used
6-5	SPARE 6-5	SPARE	Sensor input not used
6-6	SPARE 6-6	SPARE	Sensor input not used
6-7	SPARE 6-7	SPARE	Sensor input not used
6-8	SPARE 6-8	SPARE	Sensor input not used
6-9	SPARE 6-9	SPARE	Sensor input not used
6-10	SPARE 610	SPARE	Sensor input not used
6-11	SPARE 6-11	SPARE	Sensor input not used
6-12	SPARE 6-12	SPARE	Sensor input not used
6-13	SPARE 6-13	SPARE	Sensor input not used
6-14	SPARE 6-14	SPARE	Sensor input not used
6-15	SPARE 6-15	SPARE	Sensor input not used
6-16	SPARE 6-16	SPARE	Sensor input not used

### **Analog Outputs (MCS-IO-BASE)**

#	Output Name	Description
1-1	Exv%	Electronic Expansion Valve Control Signal
1-2	StgValve1%	Compressor 1 Staging Valve
1-3	StgValve2%	Compressor 2 Staging Valve
1-4	StgValve3%	Compressor 3 Staging Valve

### **Analog Outputs (MCS-IO-EXT)**

1-1	Demand 1%	Compressor 1 Speed Demand
1-2	SPARE1-2	Analog input not used
1-3	SPARE1-3	Analog input not used
1-4	SPARE1-4	Analog input not used

### **Analog Outputs (MCS-SI-BASE)**

2-1	Demand 2%	Compressor 2 Speed Demand
2-2	SPARE2-2	Analog input not used
2-3	SPARE2-3	Analog input not used
2-4	SPARE2-4	Analog input not used

### **Analog Outputs (MCS-IO-EXT)**

3-1	Demand 3%	Compressor 2 Speed Demand
3-2	SPARE2-2	Analog input not used
3-3	SPARE2-3	Analog input not used
3-4	SPARE2-4	Analog input not used


# Sample Questionnaire

 $\textit{Visit}\ \underline{\textit{https://www.mcscontrols.com/brochures.html}}\ \textit{for a fillable form to email to sales@mcscontrols.com}$ 

	formation
Company:	Phone:
Name:	Title:Email:
Mobile:	Site:
Unit Inforn	
Installation	Site Name
Model#_	Unit Serial # Site Unit #
What is th	e Voltage of the Unit? 208V, 230V, 460V, 4160V, Other Voltage
What is th	e Control voltage in the unit?
Is MCS m	onitoring Main Voltage? Yes No. Will Phase loss need to be monitored? Yes No.
1. Integr	ating to Building Management System (BMS)
Motor Info	
	is the Starter Type?
b	The a Variable Frequency Described R CLICKON THE  What is the VFD Make and Model? VFD Make  Will the VFD be hardwired to MCS to t R, o et 10 DE BELOW  Is MCS required to control VFD Cabinet Auxiliary Fan?  Yes No.
	are the Motor "RUN LOAD AMPS'(FLA)?
	Gas Bypass present?
Purge Info	
	is the Purge Type on the unit, how is it controlled ?
7. Is MC	S controlling the chiller Water Pump(s)?
8. Is MC	S controlling the Condenser water Pump(s)?
9. Is MC	S controlling Condenser/Evaporator Isolation Valve? Yes No BMS.
10. Is MC	S controlling tower fan(s)?
11. Will th	e Chilled/Condenser Water Flow be measured by?
Ambient Ir	
12. Will A	mbient temperature need to be monitored? Yes No.
CVHA Info	rmation Only
13. Is ther	e a Motor Cooler? Yes No, Will MCS be monitoring the Oil Feed? Yes No, Return Tem
COMMENT	Click for Brochure Upgrades ►
	g form printed Brochure, Scan QR code from mobile device, email the form to your email address. the emailed link. Fill out the digital fillable form on a computer and email to sales@mcscontrols.com

3. Viewing brochure from Computer, click on QR code, find the form your need, click on fillable form, fill out and email to

sales@mcscontrols.com





5580 Enterprise Pkwy., Fort Myers, FL 33905 Office: 239-694-0089 • Fax: 239-694-0031 www.mcscontrols.com